



ELESA original design 1.780

Metric table

Dimensions in: millimeters - inches

¹ d ₁ +0.5	² d ₂ Color SW Color RT	d ₃	l ₁	l ₂ min.	l ₃
24 .94	M 8 M 8	20.5 .81	65 2.56	30 1.18	7 .28
24 .94	M 10 -	20.5 .81	65 2.56	40 1.57	7 .28
26 1.02	M 8 -	21 .83	80 3.15	40 1.57	7 .28
26 1.02	M 10 M 10	21 .83	80 3.15	55 2.17	7 .28
26 1.02	M 12 -	21 .83	80 3.15	55 2.17	7 .28
28 1.10	M 10 -	22.5 .89	90 3.54	58 2.28	7 .28
28 1.10	M 12 M 12	22.5 .89	90 3.54	58 2.28	7 .28

Specification

- Plastic
Technopolymer (Polyamide PA)
- Temperature resistant up to 230 °F (110 °C)
- Color (matte finish):
Black, RAL 9005
Red, RAL 3000
- RoHS compliant



Information

EN 519.2 cylindrical handles are an advanced development of the cylindrical handles EN 519 in technopolymer plastic. Thanks to the polyamide material used in the manufacturing of this part, they feature superb mechanical properties.

When using EN 519.2 cylindrical handles, the threaded portion of the shaft must be long enough so it seats completely in the handle otherwise, the plastic itself could ultimately fail under excessive stress.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Cylindrical Handles EN 519 (Phenolic Plastic)
- Softline Cylindrical Handles EN 519.6

How to order	1	Handle diameter d ₁
¹ ² ³ EN 519.2-26-M10-RT	2	Thread d ₂
	3	Color