



ELESA original design I.281



4 Type

- A** With stainless steel threaded spindle
- B** With steel threaded spindle
- E** Without threaded spindle

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, smooth glossy finish
- Spindle
- Type **A**:
Stainless steel
European Standard No. 1.4301 (AISI 304)
- Type **B**:
Steel, matte chrome plated finish
- RoHS compliant



KU

Information

The outstanding feature of EN 598.2 revolving handles is their highly robust design. They are resistant to solvents, oils, grease and other chemical agents.

Type E is suitable for use with user-specific threaded spindle.

see also...

- *Revolving Handles GN 598.1 (with Stainless Steel Threaded Spindle)*

How to order (Inch, with threaded spindle)

EN 598.2-KU-18-1/4X20-B

- 1** Material
- 2** Handle diameter d_1
- 3** Thread d_2
- 4** Type

How to order (Metric, without threaded spindle)

EN 598.2-KU-26-13-E

- 1** Material
- 2** Handle diameter d_1
- 3** Bore diameter d_3
- 4** Type

Inch table

Dimensions in: inches - millimeters

² d ₁	³ d ₂ Type B	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	A/F Internal hexagon
.71 18	1/4 x 20*	.59 15	.47 12	1.57 40	.51 13	.04 1	1.54 39	1.38 35	.31 8	.16 4
.83 21	5/16 x 18*	.67 17	.55 14	1.97 50	.59 15	-	1.97 50	1.69 43	.39 10	.20 5
.91 23	5/16 x 18*	.75 19	.63 16	2.56 65	.67 17	.04 1	2.52 64	2.20 56	.47 12	.24 6
1.02 26	3/8 x 16*	.83 21	.67 17	3.15 80	.71 18	.04 1	3.11 79	2.76 70	.47 12	.24 6
1.10 28	3/8 x 16*	.87 22	.75 19	3.54 90	.71 18	.04 1	3.50 89	3.11 79	.47 12	.31 8

* Inch sizes are only available with steel threaded stud

Metric table

Dimensions in: millimeters - inches

² d ₁	³ d ₂ 6g Type A, Type B	³ d ₃ ^{+0.3 +0.1} Type E	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	A/F Internal hexagon	
18 .71	M 6	-	8 .31	15 .59	12 .47	40 1.57	13 .51	1 .04	39 1.54	35 1.38	8 .31	4 .16
21 .83	M 8	-	10 .39	17 .67	14 .55	50 1.97	15 .59	-	50 1.97	43 1.69	10 .39	5 .20
23 .91	M 8	-	12 .47	19 .75	16 .63	65 2.56	17 .67	1 .04	64 2.52	56 2.20	12 .47	6 .24
23 .91	M 10	-	12 .47	19 .75	16 .63	65 2.56	17 .67	1 .04	64 2.52	56 2.20	11 .43	6 .24
26 1.02	M 10	-	13 .51	21 .83	17 .67	80 3.15	18 .71	1 .04	79 3.11	70 2.76	12 .47	6 .24
28 1.10	M 10	-	14 .55	22 .87	19 .75	90 3.54	18 .71	1 .04	89 3.50	79 3.11	12 .47	8 .31
31 1.22	M 12	M 14	16 .63	25 .98	20 .79	102 4.02	20 .79	2 .08	100 3.94	89 3.50	13 .51	8 .31