



ELESA original design VRTP+I-SST



Stainless Steel



iF product design award

2 Bore code

- B Without keyway
- K With keyway

4 Type

- R With revolving handle

Metric table

1 d ₁	3 d ₂ H7	d ₃	d ₄	d ₅	b	l ₁	l ₂	l ₃	r	Ø Handle
80 3.15	8 .31	18 .71	20.5 .81	25 .98	18 .71	17 .67	35 1.38	45 1.77	29 1.14	16 .63
100 3.94	10 .39	18 .71	20.5 .81	25.5 1.00	20 .79	17 .67	37 1.46	60 2.36	37 1.46	18 .71
125 4.92	12 .47	22 .87	26 1.02	31 1.22	22 .87	22 .87	44 1.73	65 2.56	48 1.89	22 .87
160 6.30	14 .55	26 1.02	31 1.22	40 1.57	25 .98	27 1.06	51 2.01	80 3.15	65 2.56	23 .91
200 7.87	16 .63	30 1.18	36 1.42	48.5 1.91	28 1.10	34 1.34	61 2.40	80 3.15	84 3.31	24 .94

Specification

- Plastic
Special high-impact strength Technopolymer (Polypropylene PP)
- Certified in accordance with FDA
- Reinforced, shock-resistant
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- Stainless steel hub bushing
European Standard No. 1.4301 (AISI 304)
- Stainless steel hub cover
- European Standard No. 1.4301 (AISI 304)
- Self-adhesive
- Revolving handles
Plastic, Technopolymer (Polyamide PA)
- Black, matte finish
- Certified in accordance with FDA
- Stainless steel spindle
European Standard No. 1.4301 (AISI 304)
- RoHS compliant

Information

EN 522.5 two spoked handwheels have an ergonomically shaped rim for a safer and more comfortable grip.
Suitable for use in corrosion free environments. Specifically, the FDA certified plastic materials allow the use in the food industry.
Resistant to solvents, oils, grease and other chemical agents.

see also...

- Countersunk Washers GN 184.5 (Stainless Steel)

On request

- Special inch and metric bores

How to order

EN 522.5-125-B12-R

- 1** Handwheel diameter d₁
- 2** Bore code
- 3** Bore diameter d₂
- 4** Type