



ELESA original design EBK-p-SOFT



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂ Thread	³ Length l	d ₃	h ₁	h ₂
1.97 50	5/16 x 18	.75 19	1.42 36	2.44 62	.71 18
1.97 50	3/8 x 16	.98 25	1.42 36	2.44 62	.71 18

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	³ Length l	d ₃	h ₁	h ₂
43 1.69	M 6	16 .63	20 .79	25 .98	-
43 1.69	M 8	16 .63	20 .79	25 .98	30 1.18
43 1.69	M 10	20 .79	25 .98	30 1.18	50 1.97
50 1.97	M 8	16 .63	20 .79	25 .98	30 1.18
50 1.97	M 10	20 .79	25 .98	30 1.18	50 1.97

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Softline coating
Elastomer (TPE) 70 shore A
- Temperature resistant up to 175 °F (80 °C)
- Black-gray, matte finish, similar to RAL 7021
- Softline coating is chemically bonded with the plastic core
- Threaded stud
- Steel, zinc plated, blue passivated finish
- Molded-in
- RoHS compliant

Information

EN 675 Softline ball handles are a part of the Ergostyle® product family. The soft jacket makes the ball handles particularly ergonomic, safe and easy to grip.

The **soft, slip-proof** contact area improves the grip in oily, hot / humid (hand perspiration), dry ambient conditions, and in low (below freezing) temperatures.

The Softline ball handles are suitable for use both as operating elements and for clamping. The „hard“ plastic core guarantees the perfect anchoring of the insert with threaded stud even under heavier clamping or torquing loads.

Resistant to solvents, oils, grease and other chemical agents (avoid alcohol).

On request

- Ergostyle® Softline revolving ball handles

How to order (Inch)	¹ Ball diameter d ₁
² EN 675-50-5/16X18-19	² Thread d ₂
³	³ Length l

How to order (Metric)	¹ Ball diameter d ₁
² EN 675-43-M8-20	² Thread d ₂
³	³ Length l