



Metric table

Dimensions in: millimeters - inches

² d_1 Handle diameter	³ d_2 Thread			d_3	d_4	l_1	l_2	$l_3 \approx$	l_4
16 .63	M 6	-	-	10 .39	13 .51	41.5 1.63	12 .47	2.5 .10	15 .59
18 .71	M 6	M 8	-	10 .39	14.5 .57	56 2.20	13 .51	2.5 .10	19 .75
22 .87	M 6	M 8	M 10	14 .55	18.5 .73	59 2.32	14 .55	2.5 .10	21 .83
24 .94	M 8	M 10	-	14 .55	18.5 .73	74 2.91	16 .63	2.5 .10	27 1.06
25 .98	M 10	-	-	16 .63	20 .79	84 3.31	16 .63	2.5 .10	30 1.18

Specification

- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 194 °F (90 °C)
- Black, matte finish
- Aluminum **AL**
Polished finish
- Spindle
Steel, zinc plated, blue passivated finish, with internal hexagon
- RoHS compliant

Information

- GN 798 stepped cylindrical revolving handles are noted for their modern design, and the stepped shape provides the operator with a more secure grip.
- see also...
- Stepped Cylindrical Revolving Handles GN 798.2 (plastic, tapped type)
 - Stepped Retractable Handles GN 798.3 (plastic, with steel locking mechanism)
 - Safety Retractable Handles GN 798.7 (plastic, automatic fold-down type)

How to order ¹ ² ³ GN 798-AL-24-M10	1 Material
	2 Handle diameter d_1
	3 Thread d_2