



SS Stainless Steel

Metric table



Dimensions in: millimeters - inches

d ₁	d ₂ Thread	d ₃	l ₁ ≈ (Arrested)	l ₂	l ₃	l ₄	l ₅
22 .87	M 6	20 .79	82 3.23	22 .87	5.5 .22	73 2.87	13 .51
24 .94	M 6	20 .79	97 3.82	22 .87	5.5 .22	88 3.46	13 .51
25 .98	M 6	20 .79	107 4.21	22 .87	5.5 .22	98 3.86	13 .51

Specification



- Handle
Plastic
Technopolymer (Polyamide PA) **KT**
 - Temperature resistant up to 194 °F (90 °C)
 - Black, matte finish
 - Revolving
- **GN 798.7**
Retractable mechanism
 - Stem, retaining pin
Steel 1.0718, blackened finish
 - Hub
Sintered steel, blackened finish
- **GN 798.8**
Retractable mechanism
Stainless steel
 - Stem, retaining pin
European Standard No. 1.4305 (AISI 303)
 - Hub
Sintered steel
European Standard No. 1.4404 (AISI 316 LHC)
- RoHS compliant

Information

GN 798.7 and GN 798.8 stepped safety retractable handles are suitable for applications where the handle must not remain in the operating position.

In order to bring the handle into the operating position, it has to be pulled up 90° from its retracted position against a torsion spring to a stop, and then it is pushed against spring pressure into its hold position.

By maintaining the forward thrust on the handle, the handwheel can easily be rotated.

When releasing the handle, the spring automatically returns it back to the retracted position.

How to order (Steel) GN 798.7-KT-25	1 Material
	2 Handle diameter d₁

How to order (Stainless steel) GN 798.8-KT-24	1 Material
	2 Handle diameter d₁