



ELESA original design VRU. / VRU +I

2 Bore code

B Without keyway

4 Type

A Without handle

D With revolving handle

Metric table

Dimensions in: millimeters - inches

1 d ₁	3 d ₂ H9 Bore	d ₃	d ₆	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
125 4.92	10 .39	55 2.17	32 1.26	18 .71	15 .59	22 .87	28 1.10	65 2.56	47 1.85	23 .91	M 8
160 6.30	10 .39	70 2.76	42 1.65	22 .87	17 .67	26 1.02	35 1.38	65 2.56	60 2.36	23 .91	M 8
200 7.87	12 .47	85 3.35	53 2.09	26 1.02	20 .79	27 1.06	40 1.57	80 3.15	75 2.95	26 1.02	M 10
250 9.84	12 .47	105 4.13	68 2.68	30 1.18	22 .87	30 1.18	49 1.93	80 3.15	99 3.90	26 1.02	M 10

Specification

- Plastic
High strength Duroplast (Phenolic PF)
- Reinforced
- Black, glossy finish
- Hub bushing
Steel, black oxid finish, molded-in
- Revolving handles
Plastic, Duroplast (Phenolic PF)
- Black, glossy finish
- Threaded spindle
Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

Information

EN 940 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents. No mounting hole in handwheel rim for handwheel without handle, handle shipped loose; mounting of handle is required.

On request

- Special inch or metric bores larger than listed
- Other modifications such as keyways, set screw holes, etc.

How to order

EN 940-125-B10-A

- 1** Handwheel diameter d₁
- 2** Bore code
- 3** Bore diameter d₂
- 4** Type