



ELESA Original design I.701+x / I.731+x

4 Type

- A Without finger molding
- B With finger molding

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	3 l ₁	b	d ₃	l ₂
13.5 .53	M 4	20 .79	11 .43	11 .43	8 .31
13.5 .53	M 5	20 .79	11 .43	11 .43	10 .39
16 .63	M 5	23 .91	13 .51	12.5 .49	10 .39

Specification

- Plastic
Technopolymer (Polyamide PA)
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- Threaded spindle
Steel, zinc plated finish
- RoHS compliant

Information

EN 595 mini revolving handles are used, for example, in connection with small handwheels or cranked handles with low adjustment torque. Finger moldings in Type B provide additional safety against slipping and make operation easier.

<p>How to order</p> <p>1 2 3 4</p> <p>EN 595-13.5-M5-20-A</p>	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l ₁
	4 Type