



ELESA original design VRU. / VRU +I

2 Bore code

B Without keyway

4 Type

A Without handle

D With revolving handle

Universal table

Dimensions in: millimeters - inches

1 d ₁	3 d ₂ H9 Bore	d ₃	d ₆	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
125 4.92	10 .39	55 2.17	32 1.26	18 .71	15 .59	22 .87	28 1.10	65 2.56	47 1.85	23 .91	M 8
160 6.30	10 .39	70 2.76	42 1.65	22 .87	17 .67	26 1.02	35 1.38	65 2.56	60 2.36	23 .91	M 8
200 7.87	12 .47	85 3.35	53 2.09	26 1.02	20 .79	27 1.06	40 1.57	80 3.15	75 2.95	26 1.02	M 10
250 9.84	12 .47	105 4.13	68 2.68	30 1.18	22 .87	30 1.18	49 1.93	80 3.15	99 3.90	26 1.02	M 10

Specification

- Plastic
Duroplast (Phenolic PF)
- High strength reinforced
- Black, glossy finish
- Hub bushing
Steel, black oxid finish, molded-in
- Revolving handles
Plastic, Duroplast (Phenolic PF)
- Black, glossy finish
- Threaded spindle
Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- *Plastic Characteristics*
- **RoHS compliant**

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

EN 940 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

How to order

EN 940-125-B10-A

1	Handwheel diameter d ₁
2	Bore code
3	Bore diameter d ₂
4	Type