



ELESA original design IEL-x SOFT



Metric table

Dimensions in: millimeters - inches

| <sup>1</sup> d <sub>1</sub> | <sup>2</sup> l <sub>1</sub> | <sup>3</sup> d <sub>2</sub><br>Thread |      | d <sub>3</sub> | d <sub>4</sub> | l <sub>2</sub> | l <sub>3</sub> ≈ |
|-----------------------------|-----------------------------|---------------------------------------|------|----------------|----------------|----------------|------------------|
| 45<br>1.77                  | 47<br>1.85                  | -                                     | M 10 | 12<br>.47      | 28<br>1.10     | 17<br>.67      | 1<br>.04         |
| 45<br>1.77                  | 64<br>2.52                  | M 8                                   | M 10 | 12<br>.47      | 21<br>.83      | 17<br>.67      | 1<br>.04         |

Specification

- Plastic  
Technopolymer (Polypropylene PP)  
- Softline coating  
Elastomer (TPE) 70 shore A  
- Chemically bonded with the plastic core  
- Temperature resistant up to 175 °F (80 °C)  
- Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

EN 597.1 revolving mushroom shaped knobs are used in applications that require friction-free turning action, such as vertically positioned handwheels or cranked handles.  
The semi-hard material used, along with the knob shape, makes it very operator-friendly.  
The soft, slip-proof cover improves grip both in hot (hand sweat) and in dry ambient conditions, as well as in the event of oily surfaces and in very high or very low (freezing) temperatures.

see also...

- Product Range Softline
- Revolving Ball Knobs GN 319.2

|   |   |                                |
|---|---|--------------------------------|
| <p>How to order</p> <p><sup>1</sup> <sup>2</sup> <sup>3</sup></p> <p>EN 597.1-45-47-M10</p> | 1 | Handle diameter d <sub>1</sub> |
|   | 2 | Length l <sub>1</sub>          |
|   | 3 | Thread d <sub>2</sub>          |