



SS Stainless Steel

2 Bore code

- B** Without keyway
- K** With keyway

4 Type

- A** Without handle
- F** With fixed handle

Specification

- Stainless steel precision casting
 - European Standard No. 1.4401 (AISI 316)
 - Acid-resistant (A4-Quality)
 - Contact face of hub machined
 - Rim turned and highly polished
- Fixed handle DIN 39
Stainless steel
 - European Standard No. 1.4404 (AISI 316L)
 - Acid-resistant (A4-Quality)
- Wheel body
 - Unmachined body, matte shot-blasted finish
- **RoHS compliant**

Information

- The dimensions of GN 950.6 handwheels are equivalent to DIN 950 handwheels.
- No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.
- see also...**
- *Countersunk Washers GN 184.5 (for Axial Fixing)*
 - Three Spoked Handwheels DIN 950 (Cast Iron / Aluminum)

On request

- Other modifications such as metric and inch size round and square bores, keyways, set screw holes, etc.

<p>How to order</p> <p style="text-align: center;"> 1 2 3 4 </p> <p style="font-size: 1.2em; font-weight: bold;">GN950.6-100-B1/2-A</p>	1 Handwheel diameter d_1
	2 Bore code
	3 Bore diameter d_2
	4 Type

<p>How to order</p> <p style="text-align: center;"> 1 2 3 4 </p> <p style="font-size: 1.2em; font-weight: bold;">GN950.6-100-K10-F</p>	1 Handwheel diameter d_1
	2 Bore code
	3 Bore diameter d_2
	4 Type

Inch table

Dimensions in: inches - *millimeters*

d₁	d₂ +0.002 Bore	d₃ ≈	d₄	b	l₁	l₂ ≈	l₃	r	Ø Handle	No. of spokes
3.94 100	1/2	1.00 25.5	M 6	.57 14.5	.67 17	1.30 33	1.91 48.5	1.42 36	.63 16	3
4.92 125	1/2	1.06 27	M 8	.62 15.8	.71 18	1.40 35.5	2.44 62	1.85 47	.79 20	3
5.51 140	5/8	1.14 29	M 8	.67 17	.75 19	1.52 38.5	2.44 62	2.05 52	.79 20	3
6.30 160	5/8	1.22 31	M 10	.69 17.5	.79 20	1.56 39.5	3.03 77	2.44 62	.98 25	3
7.87 200	3/4	1.46 37	M 10	.79 20	.94 24	1.75 44.5	3.03 77	3.15 80	.98 25	3

Metric table

Dimensions in: millimeters - *inches*

d₁	d₂ H9 Bore	d₃ ≈	d₄	b	l₁	l₂ ≈	l₃	r	Ø Handle	No. of spokes
100 3.94	10	25.5 1.00	M 6	14.5 .57	17 .67	33 1.30	48.5 1.91	36 1.42	16 .63	3
125 4.92	12	27 1.06	M 8	15.8 .62	18 .71	35.5 1.40	62 2.44	47 1.85	20 .79	3
140 5.51	14	29 1.14	M 8	17 .67	19 .75	38.5 1.52	62 2.44	52 2.05	20 .79	3
160 6.30	14	31 1.22	M 10	17.5 .69	20 .79	39.5 1.56	77 3.03	62 2.44	25 .98	3
200 7.87	18	37 1.46	M 10	20 .79	24 .94	44.5 1.75	77 3.03	80 3.15	25 .98	3

 1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4
