



- 3 Type**
- D with plain shaft
 - E with threaded shaft

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ h8 Type D		d ₃ Type E		d ₄ h13	l ₁ ≈	l ₂	l ₃	A/F Internal hexagon
	ST / AL	KT	ST / AL	KT					
16 .63	7 .28	7 .28	M 6	M 6	10 .39	49 1.93	11 .43	5.5 .22	3 .12
20 .79	8 .31	8 .31	M 8	M 8	13 .51	61 2.40	13 .51	6 .24	4 .16
25 .98	10 .39	10 .39	M 10	M 10	16 .63	75 2.95	14 .55	8 .31	5 .20
32 1.26	13 .51	13 .51	M 12	M 12	20 .79	95 3.74	21 .83	10.5 .41	6 .24
36 1.42	16 .63	-	M 16	-	22 .87	106 4.17	26 1.02	11 .43	8 .31

Specification

- Steel **ST**
Zinc plated, blue passivated finish
- Aluminum **AL**
Turned and polished
- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Spindle
Steel, zinc plated, blue passivated finish

Information

DIN 98 revolving handles have a comfortable grip and are widely used on crank handles or handwheels. Type D handles are supplied unassembled so that the shaft can be press-fit or screwed into a tapped blind bore prior to assembly. During mounting, easy blows with a soft hammer are sufficient to drive the handle into place.

<p>How to order</p> <p>DIN 98-KT-20-E</p>	1	Material
	2	Handle diameter d ₁
	3	Type