



**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> ≈ (Arrested)	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>
23 .91	M 6	20 .79	79 3.11	88 3.46	22 .87	13 .51	5.5 .22
26 1.02	M 6	20 .79	93 3.66	102 4.02	22 .87	13 .51	5.5 .22

**Specification**

- Handle  
Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, smooth glossy finish  
- Revolving
- Retractable mechanism  
Steel, blackened finish
- RoHS compliant



**KU**

**Information**

GN 598.7 safety retractable handles are suitable for applications where the handle must not remain in the operating position.

In order to bring the handle into the operating position, it has to be pulled up 90° from its retracted position against a torsion spring to a stop, and then it is pushed against spring pressure into its hold position.

By maintaining the forward thrust on the handle, the handwheel can easily be rotated.

When releasing the handle, the spring automatically returns it back to the retracted position.

How to order

**GN 598.7-KU-26**

1 **Material**

2 **Handle diameter d<sub>1</sub>**