



ELESA original design VR.FP / VR.FP I

2 Bore Code
BLANK Without Bore

3 Type
A Without handle
D With revolving handle

Inch table

1 d ₁	2 Bore	d ₂	d ₃	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
3.94 100	Blank	.94 24	.79 20	.55 14	1.42 36	.47 12	1.57 40	1.57 40	1.46 37	.71 18	M 6
4.92 125	Blank	.94 24	.79 20	.71 18	1.42 36	.47 12	1.77 45	1.97 50	1.85 47	.83 21	M 8
6.30 160	Blank	1.26 32	.94 24	.87 22	1.50 38	.59 15	1.97 50	2.56 65	2.32 59	.91 23	M 8
7.09 180	Blank	1.57 40	1.22 31	.94 24	1.69 43	.59 15	2.20 56	3.15 80	2.68 68	1.02 26	M 10
7.87 200	Blank	1.57 40	1.22 31	.94 24	1.69 43	.59 15	2.20 56	3.15 80	2.99 76	1.02 26	M 10
9.84 250	Blank	1.93 49	1.50 38	1.18 30	1.73 44	.59 15	2.60 66	3.54 90	3.86 98	1.10 28	M 10
11.42 290	Blank	2.28 58	1.85 47	1.26 32	2.20 56	.71 18	3.07 78	3.94 100	4.45 113	1.22 31	M 12
14.76 375	Blank	2.28 58	2.28 58	1.57 40	3.03 77	1.02 26	4.25 108	3.94 100	6.30 160	1.22 31	M 14

Dimensions in: inches - millimeters

Specification

- Plastic
High strength Duroplast (Phenolic PF)
- Reinforced
- Black, glossy finish
- Hub bushing
Steel, black oxid finish, molded-in
- Revolving handles
Plastic, Duroplast (Phenolic PF)
- Black glossy finish
- Threaded spindle
Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

On request

- Other modifications such as inch or metric bores, keyways, set screw holes, etc.

Information

EN 950 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents.

How to order	1 Handwheel diameter d ₁
1 2 3 EN 950-180-BLANK-D	2 Bore code
	3 Type