



### Specification

- Mount body  
Natural rubber (NR), vulcanized, 55 durometer (shore hardness +/-5°)
- Cover plate and threaded stud  
Steel, zinc plated, molded in  
- With 2 threaded studs
- RoHS compliant

### On request

- Versions with 40 or 70 durometer natural rubber material available in certain minimum quantities
- Specials, with certain minimum quantities

### Information

GN 351.1 vibration isolation mounts, also known as vibration mounts, anti-vibration mounts, vibration bobbins or rubber bumpers, are suitable for the elastic mounting of machine units such as motors, compressors and pumps.

These rubber mounts are simple and economical construction elements. Their resilience and their broad range of different sizes and dimensions allow these mounts to be used in many applications that require vibration isolation.

For metric versions see GN 351.

#### see also...

- *Vibration Isolation Mounts GN 351.2* → page XYZ
- *Vibration Isolation Mounts GN 351* → page XYZ
- *Vibration Isolation Mounts GN 351.3* → page XYZ

### How to order (Vibration Isolation Mount)

How to order ()	1	$d_1$
	2	$h$
	3	$d_2$
	4	Hardness

351.1-10-13-8X32-55

**Inch table**Dimensions in: inches - *millimeters*

<b>d<sub>1</sub></b>	<b>h</b>	<b>d<sub>2</sub> Thread</b>	<b>l Stud Length</b>	<b>s</b>
.39 10	.51 13	8 x 32 8 x 32	.51 13	.04 1
.55 14	.51 13	10 x 32 10 x 32	.39 10	.04 1
.63 16	.51 13	8 x 32 8 x 32	.51 13	.05 1.2
.75 19	.75 19	1/4 x 20 1/4 x 20	.51 13	.08 2
.98 25	.51 13	1/4 x 20 1/4 x 20	.51 13	.08 2
.98 25	.75 19	1/4 x 20 1/4 x 20	.63 16	.08 2
.98 25	.75 19	5/16 x 18 5/16 x 18	.63 16	.08 2
.98 25	.98 25	1/4 x 20 1/4 x 20	.51 13	.08 2
.98 25	.98 25	5/16 x 18 5/16 x 18	.63 16	.08 2
1.26 32	.75 19	1/4 x 20 1/4 x 20	.51 13	.08 2
1.26 32	.75 19	5/16 x 18 5/16 x 18	.63 16	.08 2
1.26 32	.98 25	5/16 x 18 5/16 x 18	.63 16	.08 2
1.38 35	.98 25	5/16 x 18 5/16 x 18	.63 16	.08 2
1.50 38	.75 19	5/16 x 18 5/16 x 18	.63 16	.08 2
1.50 38	.98 25	3/8 x 16 3/8 x 16	.63 16	.08 2
1.57 40	.98 25	3/8 x 16 3/8 x 16	.63 16	.08 2
1.57 40	.98 25	5/16 x 18 5/16 x 18	.63 16	.08 2
2.01 51	.75 19	3/8 x 16 3/8 x 16	1.14 29	.08 2
2.01 51	1.61 41	3/8 x 16 3/8 x 16	.63 16	.08 2
2.44 62	1.26 32	1/2 x 13 1/2 x 13	.87 22	.08 2
3.11 79	2.24 57	1/2 x 13 1/2 x 13	1.26 32	.12 3