



ELESA original design EBK.SOFT



Inch table

Dimensions in: inches - millimeters

1		2						
d ₁	d ₂ Thread			d ₃	h ₁	h ₂ ≈	t	
1.97 50	5/16 x 18*			3/8 x 16*	1.46 37	2.52 64	.79 20	1.02 26

Metric table

Dimensions in: millimeters - inches

1		2							
d ₁	d ₂ Thread			d ₃	d ₄	h ₁	GN 675.1	h ₂ ≈	t
43 1.69	M 6*	M 8	M 10	32.5 1.28	20 .79	55 2.17	53.5 2.11	17.5 .69	18 .71
50 1.97	M 8	M 10	M 12	37 1.46	25 .98	64 2.52	60 2.36	20 .79	26 1.02

* Only available for EN 675

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Softline coating
Elastomer (TPE) 70 shore A
- Temperature resistant up to 176 °F (80 °C)
- Black-gray, matte finish, similar to RAL 7021
- Softline coating is chemically bonded with the plastic core
- Tapped insert
Brass
- Color of the cap (EN 675.1):
Transparent ● DTR
Orange, RAL 2004 ● DOR
Gray, RAL 7035 ● DGR
Yellow, RAL 1021 ● DGB
Blue, RAL 5024 ● DBL
Red, RAL 3000 ● DRT
- RoHS compliant

Information

EN 675 and EN 675.1 Softline ball handles are a part of the Ergostyle® product family. The soft jacket makes the ball handles particularly ergonomic, safe and easy to grip.

The **soft, slip-proof** contact area improves the grip in oily, hot / humid (hand perspiration), dry ambient conditions, and in low (below freezing) temperatures.

The Softline ball handles are suitable for use both as operating elements and for clamping. The “hard” plastic core guarantees the perfect anchoring of the tapped insert even under heavier clamping or torquing loads.

The transparent sight cap (DTR) allows symbols to be placed underneath.

Resistant to solvents, oils, grease and other chemical agents (avoid alcohol).

see also...

- Product Range Ergostyle®
- Product Range Softline

How to order (without cap)		
1	Handle diameter d ₁	
2	Thread d ₂	
EN 675-50-5/16X18		

How to order (with cap)		
1	Handle diameter d ₁	
2	Thread d ₂	
3	Color of the cap	
EN 675.1-43-M8-DBL		