



ELESA original design EKK-B



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂ Thread	d ₃	h ₁	h ₂	t min.
.83 21	10 x 32	.49 12.5	.71 18	.41 10.5	.39 10
.98 25	1/4 x 20	.57 14.5	.89 22.5	.55 14	.47 12
1.22 31	5/16 x 18	.73 18.5	1.06 27	.67 17	.63 16

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₃	h ₁	h ₂	t min.
16 .63	M 3	8.5 .33	13 .51	8.5 .33	6 .24
18 .71	M 4	10.5 .41	15.5 .61	10.5 .41	6 .24
21 .83	M 4	12.5 .49	18 .71	10.5 .41	10 .39
21 .83	M 5	12.5 .49	18 .71	10.5 .41	10 .39
25 .98	M 6	14.5 .57	22.5 .89	14 .55	12 .47
25 .98	M 8	14.5 .57	22.5 .89	14 .55	12 .47
31 1.22	M 8	18.5 .73	27 1.06	17 .67	15 .59
31 1.22	M 10	18.5 .73	27 1.06	17 .67	17 .67

* Certain colors not available from stock, requires a minimum order quantity

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Color (matte finish):
Black-gray, RAL 7021 ● SG
Red, RAL 3000 ● RT
Orange*, RAL 2004 ● OR
Gray*, RAL 7035 ● GR
Yellow*, RAL 1021 ● GB
Blue*, RAL 5024 ● BL
- Tapped insert
Brass, molded-in
- RoHS compliant

Information

When used as a push-pull button, the thumb rests naturally on the concave front surface, making it easier to grip the EN 676 Ergostyle® knurled knob. The slight knurling on the rim of the knob makes tightening or clamping operations easier.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Product Range Ergostyle®
- Push / Pull Knobs GN 676.1 (steel)
- Push / Pull Knobs GN 676.5 (stainless steel)
- Mushroom Shaped Knobs GN 76 (Phenolic plastic)

How to order	1	Handle diameter d ₁
¹ ² ³ EN 676-21-10X32-SG	2	Thread d ₂
	3	Color