



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₃	d ₄	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈
21 .83	M 5	7 .28	2.5 .10	66.5 2.62	16.5 .65	8 .31	50 1.97	69 2.72	19 .75	4 .16	6.3 .25
23 .91	M 6	8 .31	2.5 .10	86.5 3.41	16.5 .65	8 .31	70 2.76	92 3.62	21 .83	4 .16	7.5 .30
26 1.02	M 6	8 .31	2.5 .10	110 4.33	20 .79	10 .39	90 3.54	114 4.49	24 .94	4 .16	7.5 .30

Specification

- Plastic
Nylon
 - Temperature resistant up to 212 °F (100 °C)
 - Black, matte finish
 - Revolving
- Retractable mechanism
 - Chrome plated steel hub
 - Zinc plated steel stem
- RoHS compliant

Information

PGR retractable handles are suitable when the handle must be withdrawn during automatic operation. The handle is pulled out of its tapered seat in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions. A positive lock is achieved in the operating position by way of a tapered seat located in the hub of the mechanism.

When mounting the retracting mechanism to its mating surface, the securing pin gives the retractable handle more torque stability.

On request

- For certain minimum quantities, other handle colors

How to order ¹ ² PGR-21-M5	1 Handle diameter d ₁
	2 Thread d ₂