



Inch table

Dimensions in: inches - millimeters

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Bore diameter	$d_3$	$d_4$	$l_1$	$l_2$	$l_3$
1.19 30.2	B 1/4	.63 16.0	.62 15.7	1.80 45.7	.40 10.2	1.40 35.6
1.19 30.2	B 5/16	.63 16.0	.62 15.7	1.80 45.7	.40 10.2	1.40 35.6
1.19 30.2	B 3/8	.63 16.0	.62 15.7	1.80 45.7	.40 10.2	1.40 35.6

Specification

- Plastic  
Phenolic
  - Temperature resistant up to 300 °F (149 °C)
  - Black
  - With through hole
- RoHS compliant

Information

TAK tapered knobs can be utilized as a fixed grip knob or a revolving knob by mounting the knob via an applicable socket cap screw or, socket cap shoulder screw.

How to order <sup>1</sup> <sup>2</sup> <b>TAK-1.19-B1/4</b>	<b>1</b> Handle diameter $d_1$
	<b>2</b> Bore diameter $d_2$