



ELESA original design IEL.N SOFT



4 Type

- G** Closed version
- T** With transparent cap

Metric table

Dimensions in: millimeters - *inches*

1 d ₁	2 l ₁ Type G	Type T	3 d ₂ Bore diameter		l ₂	d ₃
45 <i>1.77</i>	47 <i>1.85</i>	-	B 12	-	34 <i>1.34</i>	28 <i>1.10</i>
45 <i>1.77</i>	65 <i>2.56</i>	65 <i>2.56</i>	B 10	B 12	50 <i>1.97</i>	23 <i>.91</i>

Specification

- Plastic
Technopolymer (Polypropylene PP)
 - Softline coating
Elastomer (TPE) 70 shore A
 - Chemically bonded with the plastic core
 - Temperature resistant up to 176 °F (80 °C)
 - Black, matte finish
- Transparent cap (Type T) with magnifying effect
- RoHS compliant

Accessory

- EN 517.1 positioning symbols
(printed on self-adhesive foil,
color silver-gray / black)

Information

Softline coating makes EN 718.1 mushroom shaped knobs ergonomical, safe and easy to handle. It improves the contact between a damp (perspiration) or dry hand, or an oily surface, whether in a cold or hot environment.

For mounting, gentle blows with a soft hammer are sufficient to drive the knob into place. The shaft end should be slightly rounded or chamfered (30°).

The transparent sight glass (Type T) allows symbols or similar markings to be displayed. Once the knob has been mounted to the shaft, the symbol is placed into the recess of the separately supplied sight glass, which is then carefully pushed or driven into the handle.

The symbol is fully protected from dirt and liquid by the tight connection between the sight glass and the knob.

EN 517.1 positioning symbols are to be ordered separately.

see also...

- *Product Range Softline*
- *Positioning and Control Symbols EN 517.1*
- *Tapered Knobs EN 518 (for Positioning Symbols)*

How to order	1 Handle diameter d ₁
EN 718.1-45-65-B10-G 1 2 3 4 	2 Length l ₁
	3 Bore diameter d ₂
	4 Type