



ELESA original design 1.622 / 1.622 N



Dimensions in: inches - millimeters

Inch table

¹ d ₁	² d ₂ Tapped type Only color SW	² d ₃ Press-on type Only color SW	d ₄	h	t ₁	t ₂ ±0.02	t ₃
.63 16	1/4 x 20	B 1/4	.47 12	.98 25	.63 16	.14 3.5	.67 17
.79 20	5/16 x 18	B 5/16	.55 14	1.26 32	.79 20	.14 3.5	.83 21
1.02 26	3/8 x 16	B 3/8	.67 17	1.65 42	1.18 30	.20 5	1.18 30
1.34 34	1/2 x 13	B 1/2	.83 21	2.15 54.5	1.38 35	.31 8	1.57 40

Metric table

¹ d ₁	² d ₂ Tapped type All colors, except CL		² d ₃ Press-on type Only colors SW, RT, CL			d ₄	h	t ₁	t ₂ ±0.5	t ₃
				Only colors SW, RT						
16 .63	M 6	-	B 6	-	-	12 .47	25 .98	16 .63	3.5 .14	17 .67
20 .79	M 8	-	B 8	-	-	14 .55	32 1.26	20 .79	3.5 .14	21 .83
26 1.02	-	-	-	-	B 8	17 .67	42 1.65	30 1.18	5 .20	25 .98
26 1.02	M 8	M 10	B 10	-	-	17 .67	42 1.65	30 1.18	5 .20	30 1.18
34 1.34	M 10	M 12	B 10	B 12	-	21 .83	54.5 2.15	35 1.38	8 .31	40 1.57

Specification

- Plastic
Technopolymer (Polyamide PA)
- Tapped type
Temperature resistant up to 176 °F (80 °C)
- Press-on type
Temperature resistant up to 122 °F (50 °C)
- Color (shiny finish):
Black, RAL 9005 ● SW
Orange, RAL 2004 ● OR
Gray, RAL 7035 ● GR
Yellow, RAL 1021 ● GB
Blue, RAL 5024 ● BL
Red, RAL 3000 ● RT
White, RAL 9002, Cleanline ● CL
- RoHS compliant (only color SW, GR, BL, CL)

Information

EN 719.2 domed gear lever knobs are very often used in place of DIN 319 ball knobs on gear levers and shafts. They are often selected for ergonomic reasons.

Press-on type knobs are mounted by driving them onto a gear lever shaft with a plastic hammer. A threaded shaft is not required. The shaft end should preferably be slightly rounded or chamfered (30°).

see also...

- Product Range Cleanline

How to order (Tapped type)	
¹ EN 719.2-16-1/4X20-SW	1 Handle diameter d ₁
	2 Thread d ₂
	3 Color

How to order (Press-on type)	
¹ EN 719.2-34-B10-RT	1 Handle diameter d ₁
	2 Bore diameter d ₃
	3 Color