



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

2		3							
d ₁	NI	d ₂		d ₃	d ₄	l ₁	l ₂	l ₃ ≈	l ₄
KT		Thread							
16 .63	-	M 6	-	10 .39	13 .51	41.5 1.63	12 .47	2.5 .10	15 .59
18 .71	18 .71	M 6	M 8	10 .39	14.5 .57	56 2.20	13 .51	2.5 .10	19 .75
22 .87	22 .87	M 8	M 10	14 .55	18.5 .73	59 2.32	14 .55	2.5 .10	21 .83
24 .94	24 .94	M 8	M 10	14 .55	18.5 .73	74 2.91	16 .63	2.5 .10	27 1.06
25 .98	-	M 10	-	16 .63	20 .79	84 3.31	16 .63	2.5 .10	30 1.18

Specification

- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 194 °F (90 °C)
- Black, matte finish
- Stainless steel **NI**
European Standard No. 1.4305 (AISI 303),
fine turned
- Threaded spindle
Stainless steel
European Standard No. 1.4305 (AISI 303),
with internal hexagon
- RoHS compliant

Information

GN 798.1 stepped cylindrical revolving handles are noted for their modern design, and the stepped shape provides the operator with a better grip.

see also...

- *Stepped Retractable Handles GN 798.5 (with Stainless Steel Locking Mechanism)*

How to order

1 2 3
GN 798.1-KT-16-M6

1 **Material**

2 **Handle diameter d₁**

3 **Thread d₂**