



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub>
16 .63	M 5	16 .63	58 2.28	15 .59	5 .20	52.5 2.07	9.5 .37
18 .71	M 5	16 .63	72.5 2.85	15 .59	5 .20	67 2.64	9.5 .37
22 .87	M 6	20 .79	80.5 3.17	19.5 .77	6 .24	74 2.91	10.5 .41
24 .94	M 6	20 .79	95.5 3.76	19.5 .77	6 .24	89 3.50	10.5 .41
25 .98	M 6	20 .79	105.5 4.15	19.5 .77	6 .24	98.5 3.88	10.5 .41

**Specification**

- Handle  
Plastic  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 194 °F (90 °C)  
- Black, matte finish  
- Revolving
- **GN 798.3**  
Retractable mechanism  
Steel, blackened finish
- **GN 798.5**  
Retractable mechanism  
Stainless steel  
- Stem, retaining pin  
European Standard No. 1.4305 (AISI 303)  
- Hub  
Sintered steel  
European Standard No. 1.4404 (AISI 316 LHC)
- RoHS compliant

**Information**

GN 798.3 and GN 798.5 stepped retractable handles are noted for their modern design, and the stepped shape provides the operator with a better grip.

Retractable handles are suitable when the handle must be withdrawn during automatic operations. The handle is pulled out of its taper seating in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions.

A positive lock is achieved in the operating position by way of a tapered seating.

<p>How to order (Stainless steel)</p> <p><b>GN 798.3-KT-22</b></p>	1	Material
	2	Handle diameter d <sub>1</sub>
<p>How to order (Steel)</p> <p><b>GN 798.5-KT-25</b></p>	1	Material
	2	Handle diameter d <sub>1</sub>