



2 Bore code

B Without keyway

4 Type

A Without handle

R With revolving handle

Specification



- Aluminum die casting
 - Contact face of hub machined
 - Rim turned
 - Powder coated finish
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**
- Rim concentric and square to bore < 0.4 mm
- Revolving handles GN 798.2
 - Plastic, Technopolymer
 - Black, matte finish
- RoHS compliant

Information

GN 924 flat-faced spoked handwheels are distinguished by modern design.

The removable plastic cover shrouds the mounting components such as screws, countersunk washers as well as the shaft end.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- *Two Spoked Handwheels GN 322 (Aluminum, with or without revolving handle)*
- *Countersunk Washers GN 184 (Steel)*

Accessory

- GN 184 countersunk washers are to be ordered separately

On request

- Special inch and metric bores
- Other modifications such as keyways, set screw holes, etc.

How to order

GN 924-140-B5/8-A-SW

| | |
|---|--------------------------|
| 1 | Handwheel diameter d_1 |
| 2 | Bore code |
| 3 | Bore diameter d_2 |
| 4 | Type |
| 5 | Color |

Inch table

1 **3**

Dimensions in: inches - *millimeters*

| d₁ | d₂ +0.001 Bore | d₃ | d₄ | b | h | l₁ | l₂ ≈ | l₃ ≈ | r | Ø Handle GN 798.2 | Recommended countersunk washer |
|----------------------|----------------------------------|----------------------|----------------------|--------------------|--------------------|----------------------|------------------------|------------------------|---------------------|--------------------------|---------------------------------------|
| 4.92 <i>125</i> | 1/2 | 1.22 <i>31</i> | .91 <i>23</i> | .59 <i>15</i> | .43 <i>11</i> | .71 <i>18</i> | 1.32 <i>33.5</i> | 2.42 <i>61.5</i> | 1.79 <i>45.5</i> | .87 <i>22</i> | 184-20 |
| 5.51 <i>140</i> | 5/8 | 1.42 <i>36</i> | 1.12 <i>28.5</i> | .65 <i>16.5</i> | .51 <i>13</i> | .75 <i>19</i> | 1.44 <i>36.5</i> | 3.01 <i>76.5</i> | 2.05 <i>52</i> | .94 <i>24</i> | 184-25 |
| 6.30 <i>160</i> | 5/8 | 1.42 <i>36</i> | 1.12 <i>28.5</i> | .71 <i>18</i> | .57 <i>14.5</i> | .79 <i>20</i> | 1.56 <i>39.5</i> | 3.01 <i>76.5</i> | 2.40 <i>61</i> | .94 <i>24</i> | 184-25 |
| 7.87 <i>200</i> | 3/4 | 1.65 <i>42</i> | 1.42 <i>36</i> | .81 <i>20.5</i> | .63 <i>16</i> | .94 <i>24</i> | 1.79 <i>45.5</i> | 3.35 <i>85</i> | 3.05 <i>77.5</i> | .98 <i>25</i> | 184-32 |

Metric table

1 **3**

Dimensions in: millimeters - *inches*

| d₁ | d₂ H7 Bore | | d₃ | d₄ | b | h | l₁ | l₂ ≈ | l₃ ≈ | r | Ø Handle GN 798.2 | Recommended countersunk washer |
|----------------------|------------------------------|----|----------------------|----------------------|--------------------|--------------------|----------------------|------------------------|------------------------|---------------------|--------------------------|---------------------------------------|
| 125 <i>4.92</i> | 12 | 14 | 31 <i>1.22</i> | 23 <i>.91</i> | 15 <i>.59</i> | 11 <i>.43</i> | 18 <i>.71</i> | 33.5 <i>1.32</i> | 61.5 <i>2.42</i> | 45.5 <i>1.79</i> | 22 <i>.87</i> | 184-20 |
| 140 <i>5.51</i> | 14 | 16 | 36 <i>1.42</i> | 28.5 <i>1.12</i> | 16.5 <i>.65</i> | 13 <i>.51</i> | 19 <i>.75</i> | 36.5 <i>1.44</i> | 76.5 <i>3.01</i> | 52 <i>2.05</i> | 24 <i>.94</i> | 184-25 |
| 160 <i>6.30</i> | 14 | 16 | 36 <i>1.42</i> | 28.5 <i>1.12</i> | 18 <i>.71</i> | 14.5 <i>.57</i> | 20 <i>.79</i> | 39.5 <i>1.56</i> | 76.5 <i>3.01</i> | 61 <i>2.40</i> | 24 <i>.94</i> | 184-25 |
| 200 <i>7.87</i> | 18 | 20 | 42 <i>1.65</i> | 36 <i>1.42</i> | 20.5 <i>.81</i> | 16 <i>.63</i> | 24 <i>.94</i> | 45.5 <i>1.79</i> | 85 <i>3.35</i> | 77.5 <i>3.05</i> | 25 <i>.98</i> | 184-32 |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

